QUEST 6 SERIES (GEN 2)

EXHAUST DUCT INSTALLATION GUIDE

AIR CAN ENTER INTO THE UNIT IN TWO WAYS:

A USE RECTANGULAR DUCT (NOT INCLUDED)

- Attach ITEM 2 (duct adapter) to ITEM 1 (unit) using 10 of ITEM 4 (screws).
- 2. Attach rectangular ducting (not provided) directly to **ITEM 2** (duct adapter).

Note: ITEM 3 will not be needed for use with rectangular duct.

- B USE (2) 14" ROUND DUCTS (NOT INCLUDED)
- 1. Attach ITEM 2 (duct adapter) to ITEM 1 (unit) using 10 of ITEM 4 (screws).
- 2. Attach ITEM 3 (14" collar Plate) to ITEM 2 (duct adapter) using 12 of ITEM 4 (screws).
- 3. Attach 14" duct (not provided) to both 14" duct openings.


⚠ CAUTION When ducting the unit, a dedicated duct system is recommended for each unit. Recommended 25' max run of ducting.

ITEM 1 6 Series Dehumidifier (not included)

ITEM 2 (1) Duct Adapter

ITEM 3 (1) 14" Collar Plate

ITEM 4 (22) #10 Srews





QUEST 6 SERIES (GEN 2)

INTAKE DUCT INSTALLATION GUIDE

AIR CAN ENTER INTO THE UNIT IN TWO WAYS:

USE RECTANGULAR DUCT (NOT INCLUDED)

- Remove both filters from unit to use in the intake ducting provided.
- 2. Attach ITEM 2 (duct adapter) to ITEM 1 (unit) using 12 of ITEM 4 (screws).
- 3. Use ITEM 7 instead of 4 if unit includes holes.
- 4. Open and remove ITEM 3 (filter door).
- 5. Slide filter into intake ducting.
- 6. Install ITEM 3 (filter door) back into position.
- 7. Attach rectangular ducting (not provided) directly to ITEM 2 (duct adapter).

Note: ITEM 6 will not be needed for use with rectangular duct.

USE (2) 14" ROUND DUCTS (NOT INCLUDED)

- Remove both filters from unit to use in intake ducting provided.
- 2. Attach ITEM 2 (duct adapter) to ITEM 1 (unit) using 12 of Item 4 (screws).
- 3. Use ITEM 7 instead of 4 if unit includes holes.
- 4. Open and remove **ITEM 3** (filter door).
- 5. Slide filter into intake ducting.
- 6. Install ITEM 3 (filter door) back into position.
- Attach ITEM 6 (14" collar plate) to ITEM 2 (duct adapter) using 12 of ITEM 4 (screws).
- 8. Attach 14" duct (not provided) to both 14" duct openings.

ITEM 1

!\ CAUTION When ducting the unit, a dedicated duct system is recommended for each unit. Recommended 25' max run of ducting.

- ITEM 1 6 Series Dehumidifier (not included)
- ITEM 2 (1) Duct Adapter (36.2" x 21.0" x 12.75")
- ITEM 3 (1) Filter Door
- ITEM 4 (12) #10 Self Drilling Screw

ITEM 5

ITEM 6 (1) 14" Collar Plate

ITEM 7 (24) #10 Screws

